



PDU specification drawing

3-Phase 400V 16A switched PDU : C13 x 48




IEC 60309 16A
3P+N+E 6hr Red PLUG

MCB or fuse :
refer to the models below

16A model :	Fuse	MCB
VP48C13-16A-WS/F_EN/2B-2	3	-
VP48C13-16A-WS/CR_EN/2B-2	-	3

Input Rating : 16A, 400V
 Inlet : 16A IEC60309 3P+N+E 6hr Red plug
 Cordset : 5-wire 2 meter 1.5mm sq. H07RN-F cordset
 Protection : 16A resettable fuse or 16A single pole hydraulic MCB x 3
 Phase Details : < **PH-1** > Output 16A max. C 13 # 1 - 16
 < **PH-2** > Output 16A max. C 13 # 1 - 16
 < **PH-3** > Output 16A max. C 13 # 1 - 16

Three phase switched PDU

Outlet : 10A Rated IEC320 C13 x 48



The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.
Copyright 2015 Synergy Global Technology Inc. All rights reserved.

Meter Features (WS Switched PDU)

Local Display : Field replaceable 2.8" color LCD with touchscreen
 Bank Measurement : Voltage (V), Current (A), energy (kWh) & power factor
 Outlet Control : Outlet Switch ON / OFF
 Accuracy : ±1% true RMS
 IP Access : via IP dongle, one IP Access up to 16 PDU Levels
 Cascade : Up to 16 PDU under single IP address via IP dongle
 SNMP : via IP dongle
 Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

EMC Compliance : FCC & CE certified
 Safety Compliance : CE / LVD certified
 Environment Compliance : RoHS2 & REACH

Operating Temperature : -5 to 60 °C
 Storage Temperature : -25 to 65 °C
 Operating Altitude : 0 to 2,000 m
 Storage Altitude : 0 to 15,000 m
 Humidity : 8 to 95% RH, non-condensing

Dimension : 85 (W) x 90 (D) x 1925 (H) mm
 Material : Steel
 Color : White (outlet bracket)
 Black (chassis)