



FEATURES

- 103 Key compact keyboard with mouse storage and use area in 1U of vertical 19" rack space.
- Mounted with included smooth action ball bearing slides which lock in the extended position.
- Convenient area in back of keyboard for easy mouse use, mouse stores behind keyboard.
- Retainer and lock options to keep unit contained in the rack when not in use.
- Housed in rugged steel construction with a durable powder coat finish.

KEYBOARD SPECIFICATIONS

| | |
|--------------------------|----------------------------|
| Keys: | 103 keys with Windows key |
| Rollover: | Alpha N-key rollover. |
| Auto repeat: | Yes. |
| Self Diagnostics: | Yes |
| Reliability: | 5M switch life cycles. |
| Pointing Device: | Optional Optical Mouse (M) |
| Interface: | USB |

GENERAL SPECIFICATIONS

| | |
|---------------------|---|
| Dimensions: | 19.0" (W) x 1.75" (H) x 20.00" (D) (22.75 D w/Cable Management) |
| Slides: | 18" (20" extension) Adjustable for 20.5" to 31.5" mounting depth. |
| Weight: | 15 lbs |
| Temperature: | Operating: 0°C to 50°C Storage: -40°C to 60°C |
| Humidity: | Operating: 20 to 90% RH Non Condensing (max) |
| Color: | Black |


Specifications subject to change without notice.



Offering OEM and custom solutions.
Contact us for additional information.

MODEL NUMBER

LCDK1066-b-bk-



Additional options and configurations available.