

ID-2-E21Aw 21" High Resolution Widescreen LCD w/ LED-backlit Display



Display Benefits

- ▶ 21.5" widescreen LCD with **Full HD 1080p** resolution
- ▶ Green LED-backlit panel technology
- ▶ Rugged construction against external impact
- ▶ Protective 3mm glass

Options

- **MC** Multi-display control solution
- 21.5" Touchscreen : Capacitive, Resistive, Multi-touch
- NEMA4 / IP65 front protective glass
- MIL-type or lockable connector
- 48V, 24V or 12VDC power

6mm aluminum front bezel with optional

NEMA 4 / IP65 front protection



Standard I/O : VGA and DVI-D

Options I/O USB for touchscreen
MC

Specifications

• LCD Panel

Manufacturer :	
Size (diagonal) :	21.5" TFT
Max resolution :	1920 x 1080
Brightness (cd/m2) :	250
Backlight :	LED
Colors :	16.7 M
Contrast ratio (typ) :	1000 : 1
Viewing angle (H/V) :	170° x 160°
Active area (mm) :	477 x 268
MTBF (hrs) :	30,000
Signal input :	DVI-D / VGA

• Weight

Net : 5 kgs (11 lbs)

• Mounting :

Panel mount / VESA mount

• Environmental

Operating :	0 to 50°C Degree
Storage :	-5 to 60°C Degree
Relative humidity :	5~90%, non-condensing
Shock :	10G acceleration (11 ms duration)
Vibration :	5~500Hz 1G RMS random vibration

• Casing Color :

Black front panel (RAL 9005)
Dark grey rear case (RAL 7037)

• Regulatory :

FCC, CE

• Power

Input :	Auto-sensing 100 to 240VAC, 50 / 60Hz
Consumption :	Max. 48 Watt, Standby 5 Watt

• Dimensions

Product : 578 x 59 x 369 mm / 22.7 x 2.3 x 14.5 inch

Diagrams (mm)

