


ID-08D 8.4" Stylish Front Aluminum Cover LCD Panel

Dimension Drawings (mm)



Applications

- Embedded display unit
- Industrial automation LCD panel
- Gaming, lottery & amusement display
- Touchscreen display panel

Options

- Touchscreen
- S-Video, RCA & BNC input
- DC power input (12 / 24 / 48 VDC)
- Audio input with speaker
- TV tuner with remote controller
- Standard remote controller for AV, VGA input

Design features

- 1.2mm front aluminum cover
- Slim, light and sophisticated
- OSD control keys to optimize the display
- Modularized design provides extra adaptability

Specifications

LCD Panel

Panel Grading	Class A TFT LCD panel
Panel Size (in.)	8.4"
Optimum Resolution	800 x 600
Display Color	262K
Brightness-nits (cd/m ²)	220
Contrast Ratio	500 : 1
Pixel Pitch (mm)	0.213 x 0.213
Viewing Angle (L/R/U/D)	65 / 65 / 65 / 45
OSD Control	Brightness, Contrast, Phase & Clock, Color, H & V position, Auto-tune & Recall
Connector(s)	D-Sub 15-pin VGA analog
LCD Panel MTBF (hrs)	50,000
Power	100 or 240VAC via AC adapter
Mounting	VESA-mount, Optional OEM mounting design
Dimensions (mm)	234 x 38 x 167 (W x D x H)

Operating Temperature

0° to 50° C

Storage Temperature

-5° to 60° C

Humidity

5~90%, non-condensing

Shock

10G peak acceleration
(11ms duration)

Vibration

5-500Hz, 1G RMS random vibration

Ordering information

Model no.	Description
ID-08D	8.4" front aluminum cover LCD panel with VGA input
ID-08DAV	8.4" front Al. cover LCD with VGA, S-Video+RCA input
ID-08DBNC	8.4" front Al. cover LCD with VGA, S-Video+BNC input
ID-08DDC12	8.4" front Al. cover LCD with VGA input, 12V DC input
ID-08DDC24	8.4" front Al. cover LCD with VGA input, 24V DC input
ID-08DDC48	8.4" front Al. cover LCD with VGA input, 48V DC input