


## 3-Phase 400V 32A switched PDU + outlet measurement : C19 x 24



32A model :	Fuse	MCB
VP24C19-32A-WSi/F_EN/2B-2/LOCK	6	-
VP24C19-32A-WSi/CR_EN/2B-2/LOCK	-	6

- Input Rating : 32A, 400V
- Inlet : 32A IEC60309 3P+N+E 6hr Red plug
- Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset
- Protection : 16A resettable fuse or 16A single pole hydraulic MCB x 6
- Bank Details : **PH-1** < **Bank 1** > Output 16A max. C 19 # C 1 - C 7 (o d d)  
< **Bank 2** > Output 16A max. C 19 # C 2 - C 8 (e v e n)
- PH-2** < **Bank 3** > Output 16A max. C 19 # C 1 - C 7 (o d d)  
< **Bank 4** > Output 16A max. C 19 # C 2 - C 8 (e v e n)
- PH-3** < **Bank 5** > Output 16A max. C 19 # C 1 - C 7 (o d d)  
< **Bank 6** > Output 16A max. C 19 # C 2 - C 8 (e v e n)

### Three phase switched PDU + outlet measurement

Outlet : 16A Rated IEC320 C19 (lockable) x 24

### Meter Features ( WSi Switched PDU + Outlet Measurement )

- Local Display : Field replaceable 2.8" color LCD with touchscreen
- Bank Measurement : Current ( A ), Energy ( kWh ), Voltage ( V ) & Power factor
- Outlet Measurement : Current ( A ), Energy ( kWh )
- Outlet Control : Outlet Switch ON / OFF
- Accuracy : ±1% true RMS
- IP Access : via IP dongle, one IP Access up to 16 PDU Levels
- Cascade : Up to 16 PDU under single IP address via IP dongle
- SNMP : via IP dongle
- Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

- EMC Compliance : FCC & CE certified
- Safety Compliance : CE / LVD certified
- Environment Compliance : RoHS2 & REACH

- Operating Temperature : -5 to 60 °C
- Storage Temperature : -25 to 65 °C
- Operating Altitude : 0 to 2,000 m
- Storage Altitude : 0 to 15,000 m
- Humidity : 8 to 95% RH, non-condensing

- Dimension : 100 (W) x 90 (D) x 1325 (H) mm
- Material : Steel
- Color : White ( outlet bracket )  
Black ( chassis )

