


IP KVM extender

- ▶ Maintaining servers across the world up to BIOS level
- ▶ Compatible with all major KVM switch for racks of server



Specifications

Model No.		IP-101	
		To computer system	To local console
Connector	Keyboard	PS/2 mini-din 6 pin (Female)	PS/2 mini-din 6 pin (Female)
	Video	VGA HD-15 pin (Female)	VGA HD-15 pin (Female)
	Mouse	PS/2 mini-din 6 pin (Female)	PS/2 mini-din 6 pin (Female)
	USB	USB type B receptacle	Nil
	Remote port	Nil	RJ-45 8P8C
	Serial port	Nil	DB-9 (Male)
Video	Bandwidth	200MHz	
	Resolution	Local : 1600 x 1200/ Remote : 1280 x 1024	
	Compatibility	SVGA, VGA, SXGA, XGA	
	Levels	0.7v P-P	
Remote web-based access		Internet, LAN/WAN, or dial-up modem	
Remote web browsers support		Microsoft® internet explorer, Netscape navigator or Mozilla	
Data encrypted		Secure socket layer SSL v2/ v3	
Power requirement to unit		DC 5V, 2.5A	
Housing		Metal	
Environment	Temperature	0 ~ 40°C	
	Humidity	0 ~ 80%	
Dimensions (cm)		14.3(W) x 15.6(D) x 2.8(H)	
Net weight		1.7kg	
Supported keyboard		PC/AT, PS/2	
Supported mouse		Standard PS/2 two button Microsoft® Intellimouse	