



Key Benefits

- ▶ 1280 x 1024 native resolution
- ▶ 16.7 M colors
- ▶ HDMI 1.4 & VGA video input ; Optional DP & DVI-D
- ▶ Video decoding capability up to 1080p (option)
- ▶ Rugged structure ensures high mobility
- ▶ Professional-use durability & around-the-clock operation

Applications

- Broadcasting / Advertising
- Traffic control / Command center
- Directory / Ticket kiosk
- Surveillance system
- Vehicle mount display
- Bathroom TV

Options

Video Management & Transmission over Network

- Multi Monitor OSD Control Module
- 3G / HD / SD-SDI Input Module
- Auto / Manual Brightness Dimming Module (for High Bright model)

Bezel & Frame Customization

- Dimension
- Color & Treatment
- Screen Printing
- Stainless Steel Bezel

Touchscreen & Glass Protection

- Resistive 1-point Touch
- Capacitive 1-point Touch
- Projected Capacitive 10-point Touch
- Anti-reflective Glass
- Vandal Proof Glass

DC Power & connector


- 12V / 24V / 48V / 110V / 125V / 250VDC
- MIL-type or lockable connector

Mounting


- VESA mount kit
- Desktop stand
- Wall mount

Diagrams (mm)


Front View



Side View



Rear View



Product Specifications

LCD Panel	ID-17D	ID-H17D
Brightness (cd/m ²)	250	1000
Contrast ratio (typ.)	1000 : 1	
MTBF (hrs)	30,000	50,000
Panel size (diagonal)	17"	
Native resolution	1280 x 1024	
Colors	16.7M	
Viewing angle (L/R/U/D)	85/85/80/80	
Response time (ms)	5	
Dot pitch (mm)	0.264	
Display area (mm)	337.92H x 270.33V	
Surface treatment	Haze 25% Hard-coating	Anti-glare
Surface hardness	3H	
Backlight type	LED	

Video	
VGA	Analog 0.7Vp-p
HDMI	HDMI 1.4 / HDCP 1.4

Video Option	
DVI-D	DVI-D single link
Composite (BNC)	NTSC & PAL

Audio	
Audio input :	
Connector	3.5mm stereo jack
Impedance / Power level	30kΩ / 750mV
Audio output :	
Connector	3.5mm stereo jack
Resistance / Power level	30kΩ / 2.8V
Speaker :	
Dual stereo speaker	2W x 2

*When the audio output is connected, speaker output is OFF

Power	ID-17D	ID-H17D
Input	Auto-sensing 100 to 240VAC, 50 / 60Hz	
Consumption :		
Screen on	Max. 22W	Max. 30W
Power saving mode	Max. 4W	Max. 4W
Power button on	Max. 1W	Max. 1W

Environment	
Operating temp.	0 to 55°C degree
Storage temp.	-20 to 60°C degree
Operating humidity	10~90%, non-condensing
Storage humidity	5 ~90%, non-condensing
Operating altitude	16,000 ft
Non-operating altitude	40,000 ft
Shock	10G acceleration (11ms duration)
Vibration	10~300Hz 0.5G RMS random vibration

Design	ID-17D / ID-H17D
Protection	Front cover
Front panel	Black, RAL 9005
Rear casing	Black, RAL 9005

Mounting	ID-17D / ID-H17D
VESA mount	100 x 100 mm
Universal mount	-
Desktop stand	option
Wall mount	option

Physical	ID-17D / ID-H17D
Product (W x D x H) :	
mm	408 x 59.5 x 325.6
inch	16.1 x 2.3 x 12.8
Net weight	5.8 kg / 12.8 lb

Compliance	
EMC	FCC & CE
Safety	CE / LVD & UKCA
Environment	REACH & RoHS3 / WEEE

VGA / DVI input	
PC signal	1280 x 1024 x 60 / 75Hz 1280 x 960 x 60Hz 1280 x 768 x 60 / 75Hz 1152 x 864 x 75Hz 1024 x 768 x 60 / 70 / 75Hz 848 x 480 x 60Hz 800 x 600 x 60 / 72 / 75Hz 720 x 400 x 70Hz 640 x 480 x 60 / 72 / 75Hz 640 x 400 x 70Hz 640 x 350 x 70Hz
Audio signal	2ch Linear PCM

HDMI input	
PC signal	Same as VGA
HDMI 1.3 / 1.2	1280 x 720 x 50 / 60Hz (720p) 720 x 480 x 50 / 60Hz (576p / 480p)
Audio signal	2ch Linear PCM