



Features & Benefits

- ▶ Easy installation with common tools
- ▶ Thin & light weight design only 3.9 kgs / 8.6 lbs
9 Fan is 4.6 kgs / 10.1 lbs
- ▶ Designed for low noise & high airflow performance
- ▶ Improves extraction of heat from high density cabinet
- ▶ Auto-sensing 110V to 220VAC power input
- ▶ 48V, 24V or 12VDC power option



Ordering Information

Model	Installation	Airflow	Purpose
RA4017-6-A	Rear door outside	Extract airflow	Exhaust air out from cabinet
RA4017-9-A	Front door inside	Intake airflow	Cool air in from aisle
RA4017-6-B	Front door outside	Intake airflow	Cool air in from aisle
RA4017-9-B	Rear door inside	Extract airflow	Exhaust air out from cabinet

* Package includes the material of clear polycarbonate plastic to block off the remaining open perforated area of the door to eliminate bypass air.

Specifications

- **Fan Panel**
 - No. of Fans : 6 / 9
 - Individual Fan CFM : 108 CFM
 - Unit CFM (approx.) : 648 CFM / 972 CFM
- **Environmental**
 - Operating : 0 to 50°C Degree
 - Storage : -5 to 60°C Degree
 - Relative humidity : 5~90%, non-condensing
 - Shock : 50G peak acceleration (11ms, half-sine wave)
 - Vibration : 58~100Hz / 0.98G (11ms / cycle)
- **Power**
 - Input : Auto-sensing
100V or 240V AC at 50 or 60Hz via IEC type cord
 - Consumption : 40W / 60W
- **Casing Color :** Black
- **Mounting :** 33U door mount
- **Safety Regulatory :** FCC & CE certified
- **Environmental :** RoHS2 & REACH compliant by SGS
- **Dimensions**
 - Product : 195 x 38.4 x 1466 mm / 7.7 x 1.5 x 57.7 inch
- **Weight**
 - Net : 6 Fan : 3.9 kgs (8.6 lbs)
9 Fan : 4.6 kgs (10.1 lbs)