



**Benefits**

- ▶ 1U 17" 4K LCD display drawer
- ▶ 3840 x 2160@60Hz native resolution / 16.7M colors ( 8-bit )
- ▶ 1920 x 1080 & 1920 x 1200 resolution support
- ▶ Display port 1.2 video input
- ▶ Built-in dual stereo speakers
- ▶ Short depth design of 480mm
- ▶ One Man installation design
- ▶ Enhanced aesthetics with molded front panel and two point lock

**Options**

- HDMI 2.0 video input
- 3G / HD / SD-SDI Broadcast-grade input
- DC power : 12V / 24V / 48V / 125V
- Touchscreen : Resistive 1-pt

**Product Specifications**

Console Port	
Video input attached 6ft DP cable	Display port 1.2

Video Option		
Digital	HDMI	HDMI 2.0 / HDCP 2.2

LCD Panel	
Panel size ( diagonal )	17.3"
Native resolution	3840 x 2160@60Hz
Brightness ( cd/m <sup>2</sup> )	300
Contrast ratio ( typ )	1000 : 1
Colors	16.7 M, 8-bit
Viewing angle ( L/R/U/D )	89/89/89/89
Response time ( ms )	16
Dot pitch ( mm )	0.0995
Display area ( mm )	382.12H x 214.94V
Surface treatment	Anti-glare
Surface hardness	3H
Backlight type	LED
MTBF ( hrs )	15,000

Mounting Distance	
Display drawer	490 ~ 720 mm 19.3 ~ 28.3 inch

Physical		
Dimensions ( W x D x H )	Product	442 x 480 x 44 mm 17.4 x 18.9 x 1.73 inch
Weight	Net	11 kg / 24.2 lb

\* All dimensions stated are subject to change if options are selected / integrated to base model part codes

Power		
Input	Auto-sensing 100 to 240VAC, 50 / 60Hz	
Consumption (console / KVM)	Screen on	Max. 21W
	Power saving mode	Max. 2W
	Power button off	Max. 1W

Environment	
Operating temp.	0 to 55°C degree
Storage temp.	-20 to 60°C degree
Operating humidity	20~90%, non-condensing
Storage humidity	5 ~90%, non-condensing
Operating altitude	16,000 ft
Non-operating altitude	40,000 ft
Shock	10G acceleration ( 11ms duration )
Vibration	10~300Hz 0.5G RMS random vibration

Compliance	
EMC	FCC & CE certified
Safety	CE / LVD certified
Environment	RoHS3 & REACH compliant

**Diagrams ( mm )**

\*\* Dimensions to be confirmed

