

Features


- Meet MIL-STD-810F/G standard
- 1U 17.3" LCD Console Drawer
- support 1920 x 1080 FHD resolution
- DVI & VGA Port
- Front 1x USB, Rear 1 x USB 2.0 Type A, Sharing USB peripheral Device for computer (ex, flash disk, hard driver, KB/Mouse)
- Sealed IP65 silicone keyboard and trackball with backlight
- MIL connector for power input
- Support USB 2.0 Keyboard & Mouse
- Self-locking and auto release rails for ultra convenience



(USB Port for device access)

Options

- HDMI, Display port input
- DC 9~36V power input
- High brightness LCD panel, up to 1000 nits



Rear of MIL1U17-03

| Part No. | | MIL1U17-03 |
|-----------------------------------|--|--|
| Direct no. of Computers | | 1 |
| LCD | Size | 17.3" |
| | Backlight | LED |
| | Resolution | 1920*1080 Full HD (support resolution up to 1920x1200) |
| | Max.color | 16.7M |
| | Luminance | 400cd/m2 |
| | View Angel (H/V) | 160 / 140 |
| | Contrast Ratio | 600 : 1 |
| USB HUB | 1x Front , 1xRear USB 2.0 Type A for Peripheral USB Device | |
| KB/Mouse Emulation | USB | |
| Rack Depth | 450mm to 600mm (rack cabinet front rails to rear rails) | |
| Power | 100-240V AC 50/60Hz via 4 pins lock connector | |
| Environment (MIL-STD-810G) | Operation temp: 0 to 50°C | (MIL-STD-810, Method 501.5 & 502.5) |
| | Storage temp: -20 to 60°C | (MIL-STD-810, Method 501.5 & 502.5) |
| | Humidity: 5% - 95%, non-condensing | (MIL-STD-810, Method 507.5) |
| | Shock/Vibration: Procedure VI, 50G @ 11ms | (MIL-STD-810, Method 516.6) |
| | Altitude: 10,000 ft Operational, 30,000 ft Storage | (MIL-STD-810, Method 500.5) |
| Physical Dimensions / Net Weights | 482x44x486mm (WxHxD) /13KG | |