


Basic Rack PDU for Blade Servers

Overview

Outlets. The PDU has six (6) IEC-320-C19 outlets and three (3) IEC-320-C13 outlets.

Power cord. The 6-ft (1.82-m) power cord terminates with an IEC-309 32 A connector.



RA5009-C-32A-IEC

Specifications

Electrical

Input connector	IEC-309, 32 A connector
Output connectors	(3) IEC-320-C13 (6) IEC-320-C19
Overload protection	(6) 16-A single-pole breakers
Max output current (outlet)	10 A-IEC-320-C13 16 A-IEC-320-C19
Max output current (phase)	32 A
Cord length	6.00 ft (1.82 m)
Nominal input voltage	230 VAC, 3-phase
Acceptable input voltage	±10% of nominal voltage
Input frequency	47–63Hz

Physical

Dimensions (H × W × D)	36.50 × 2.16 × 3.46 in (92.71 × 5.48 × 8.78 cm)
Shipping dimensions (H × W × D)	41.50 × 11.25 × 2.75 in (105.41 × 28.57 × 6.98 cm)
Weight	11.45 lb (4.27 kg)

Environmental

Elevation (above MSL)	
Operating	10,000 ft (3000 m)
Storage	50,000 ft (15 000 m)
Temperature	
Operating	23 to 140°F (–5 to 60°C)
Storage	–13 to 149°F (–25 to 65°C)
Humidity	
Operating	5–95%, non-condensing
Storage	5–95%, non-condensing

Approvals

Safety Certification	VDE, CE Mark, GOST IEC-60950, Queensland Australia
----------------------	----------------------------------------------------------
