


# PDU specification drawing

## 3-Phase 400V 32A switched PDU : C19 x 12



| 32A model :                    | Fuse     | MCB      |
|--------------------------------|----------|----------|
| VP12C19-32A-WS/F_EN/2B-2/LOCK  | <b>6</b> | -        |
| VP12C19-32A-WS/CR_EN/2B-2/LOCK | -        | <b>6</b> |

- Input Rating : 32A, 400V  
 Inlet : 32A IEC60309 3P+N+E 6hr Red plug  
 Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset  
 Protection : 16A resettable fuse or 16A single pole hydraulic MCB x 6  
 Bank Details : **PH-1 < Bank 1 >** Output 16A max. C 19 # C 1 - C 3 (odd)  
                   **< Bank 2 >** Output 16A max. C 19 # C 2 - C 4 (even)  
                   **PH-2 < Bank 3 >** Output 16A max. C 19 # C 1 - C 3 (odd)  
                   **< Bank 4 >** Output 16A max. C 19 # C 2 - C 4 (even)  
                   **PH-3 < Bank 5 >** Output 16A max. C 19 # C 1 - C 3 (odd)  
                   **< Bank 6 >** Output 16A max. C 19 # C 2 - C 4 (even)

### Three phase switched PDU

Outlet : 16A Rated IEC320 C19 (lockable) x 12

### Meter Features ( WS Switched PDU )

- Local Display : Field replaceable 2.8" color LCD with touchscreen  
 Bank Measurement : Voltage ( V ), Current ( A ), energy ( kWh ) & power factor  
 Outlet Control : Outlet Switch ON / OFF  
 Accuracy : ±1% true RMS  
 IP Access : via IP dongle, one IP Access up to 16 PDU Levels  
 Cascade : Up to 16 PDU under single IP address via IP dongle  
 SNMP : via IP dongle  
 Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

- EMC Compliance : FCC & CE certified  
 Safety Compliance : CE / LVD certified  
 Environment Compliance : RoHS2 & REACH

- Operating Temperature : -5 to 60 °C  
 Storage Temperature : -25 to 65 °C  
 Operating Altitude : 0 to 2,000 m  
 Storage Altitude : 0 to 15,000 m  
 Humidity : 8 to 95% RH, non-condensing

- Dimension : 100 (W) x 90 (D) x 1325 (H) mm  
 Material : Steel  
 Color : White ( outlet bracket )  
           Black ( chassis )